


Produktserie Lena Master Plus – Pharma

Bezeichnung der Anlage	Leistung, m ³ /hr					Anschlussleistung, W	Anschluss
	25 mJ/cm ²	40 mJ/cm ²	60 mJ/cm ²	80 mJ/cm ²	120 mJ/cm ²		
$\tau = 95\%$							
DUV-1A50-N PH MST Plus	4,5	3	2	1,5	1	260	Clamp DN 50
DUV-1A120-N PH MST Plus	9	6	4	3	2	290	Clamp DN 50
DUV-1A250-N PH MST Plus	19	12	8	6	4	380	Clamp DN 50
DUV-1A500-N PH MST Plus	25	25	18	14	9	580	Clamp DN 50
DUV-1A700-N PH MST Plus	25	25	24	19	12	680	Clamp DN 50
$\tau = 90\%$							
DUV-1A50-N PH MST Plus	3,5	2,5	1,5	1,3	-	260	Clamp DN 50
DUV-1A120-N PH MST Plus	7	5	3	2,5	-	290	Clamp DN 50
DUV-1A250-N PH MST Plus	14	10	6	5	3	380	Clamp DN 50
DUV-1A500-N PH MST Plus	25	25	16	13	8	580	Clamp DN 50
DUV-1A700-N PH MST Plus	25	25	22	17	11	680	Clamp DN 50
$\tau = 85\%$							
DUV-1A50-N PH MST Plus	3	2	1,3	1	-	260	Clamp DN 50
DUV-1A120-N PH MST Plus	6	4	2,5	2	-	290	Clamp DN 50
DUV-1A250-N PH MST Plus	12	8	5	4	2,5	380	Clamp DN 50
DUV-1A500-N PH MST Plus	25	22	15	11	7,5	580	Clamp DN 50
DUV-1A700-N PH MST Plus	25	25	20	15	10	680	Clamp DN 50
$\tau = 80\%$							
DUV-1A50-N PH MST Plus	2,5	1,8	1	-	-	260	Clamp DN 50
DUV-1A120-N PH MST Plus	5	3,5	2	-	-	290	Clamp DN 50
DUV-1A250-N PH MST Plus	10	7	4	3,5	2	380	Clamp DN 50
DUV-1A500-N PH MST Plus	25	20	13	10	6,5	580	Clamp DN 50
DUV-1A700-N PH MST Plus	25	25	18	14	9	680	Clamp DN 50

 – Der maximal zulässige Durchfluss